

Garant**Storage trolley, Number of transparent boxes: 55****Order data**

Order number	918610 55
GTIN	4062406098117
Item class	91P

Description**Version:**

Frame of hollow steel rectangular section 60×40×2 mm. Sheet metal structure with a black ABS plastic shelf. **4 castors** (2 with parking brakes, **125 mm Ø**) with treadless polyurethane tyres, roller bearing hubs and 2 push handles of Haptoprene® ensure stability and safe handling in the workshop. **Transparent tilt bins** in 4 sizes, made of transparent **ABS plastic** for dust-free storage. Tilt the transparent bins to remove stored goods. Bins can be removed and stacked for assembly purposes.

Application:

For storage / provision of bulk goods and small parts.

Fitted with:

Transparent tilt bins for the front: 18 pcs. 80×63×70 mm;

15 pcs. 100×97×108 mm;

3 pcs. 175×140×160 mm

Transparent tilt bins for the rear: 16 pcs. 128×128×133 mm;

3 pcs. 175×140×160 mm

Colour:

RAL 7035 light grey **powder coated**.

Technical description

Width	880 mm
Depth	600 mm
maximum load capacity	250 kg
Material of wheels	Treadless polyurethane tyres
Width without handle	680 mm
Number of castors with parking brake	2
Weight	67 kg
Height	1310 mm
Number of castors without parking brake	2
Wheel Ø	125 mm
Design version	Steel hollow section construction
Material thickness	1.5 mm
Hoffmann perforated panel grid interval	9×9 mm
Colour selection	RAL 9002, 7035, 7005, 7016, 6011, 5018, 5012, 5011, 5005, 3003
Type of product	Storage trolley

Accessories

Push handle Colour BLACK	920135 BLACK
Swivel castor Type 1	920137 1
Swivel castor Type 2	920137 2
Push handle Colour BLUE	920135 BLUE