

Garant GRIDLINE

Swing-door auxiliary cabinet with raised edge, 26×20G, Height: 1025mm**Order data**

Order number	932110 1025
GTIN	4062406098292
Item class	9GK

Description**Version:**

Tool auxiliary cabinet 30×28G. With swing doors, can be locked centrally with a cylinder lock. With raised edge on 3 sides and ribbed rubber mat.

An anti-tilt device prevents more than one drawer being opened at one time.

Colour:

Cabinet body and drawer body RAL 7035 light grey, drawer fronts and cupboard doors RAL 7016 anthracite, **powder-coated. Drawer body and storage shelf not configurable, always RAL 7035 light grey.**

Note:

Suitable drawers 26×20G.

Technical description

Width	750 mm
Depth	700 mm
Height	1025 mm
Electronic locking system can be retrofitted	yes

Weight	65 kg
Usable height	850 mm
Material thickness	1.2 mm
Drawer runner extension	Anti-tilt lock
Door opening angle	250 degrees
Height adjustment interval	25 mm
Cylinder lock	modular lock barrel
Colour selection	RAL 9002, 7035, 7005, 7016, 6011, 5018, 5012, 5011, 5005, 3003
Product name attribute	26x20G
Type of product	Machine auxiliary cabinet

Accessories

Slide handle for GridLine Type HU12	914226 HU12
Sheet metal cover top with raised edge on 3 sides Dimension in G 30X28	951970 30X28
Ribbed rubber mat Dimension in G 30X28	951975 30X28