



Clamping hook mounting, Length L: 100mm



Order data

Order number	370083 100
GTIN	2050001962065
Item class	37K

Description

Application:

For guiding and lifting **ground** clamping hooks.

Technical description

Thread M	M12
External \varnothing D	40 mm
\varnothing D _{F7}	25 mm
maximum torque	49 Nm
Type of product	Jig clamping system