

Cutting head, right-hand, System / insert size: QC/11S



Order data

Order number	260916 QC/11S
GTIN	4251414902732
Item class	29D

Description

Version:

Interchangeable cutting heads for **vibration-damping base bodies**. Narrow version.

Application:

Vibration damping effect up a maximum overhang of **14xD**.

Through-coolant: yes

System: QC

ISO code indexable cutting head: STUCR/L 11

suitable indexable insert: TC.. 1102..

suitable base body: 264900 – 264908

Minimum pre-drill $\varnothing D_{\min}$: 22 mm

Centre-line offset: 11 mm

Overall length: 20 mm

Technical description

Centre-line offset	11 mm
ISO code indexable cutting head	STUCR/L 11
Minimum pre-drill $\varnothing D_{\min}$	22 mm

System	QC
Insert screw	269022 4
Insert size	11 mm
Overall length	20 mm
Series	Cutting head
suitable base body	264900 – 264908
suitable indexable insert	TC.. 1102..
Shank Ø	20 mm
Application type	right-hand
Through-coolant	yes
Setting angle κ	93 degrees
Application	Internal longitudinal turning

Accessories

Torque screwdriver with scale, to take interchangeable blades maximum torque 500 cN·m	659906 500
Torx® bit, shank E 6.3 Torx® profile TX8	674248 TX8