


Garant

GARANT Master Steel solid carbide roughing end mill HPC, TiAlN, Ø f8 DC: 12mm



Order data

Order number	203034 12
GTIN	4045197718587
Item class	11X

Description

Version:

For **roughing and finishing**.

Up to $1 \times D$ into solid material **at very high feed rates** with smooth cutting action.

At maximum machining depths, ensure compliance with the ratio dimension L_c (cutting length) / \varnothing (nominal size)!

Advantage:

Optimised flute form, eccentric relief ground, wide chip space.

Technical description

Feed f_z for side milling in steel $< 900 \text{ N/mm}^2$	0.09 mm
No. of teeth Z	4
Feed f_z for slot milling in steel $< 900 \text{ N/mm}^2$	0.07 mm
Corner chamfer width at 45°	0.24 mm
Cutting edge $\varnothing D_c$	12 mm
Shank $\varnothing D_s$	12 mm
Overall length L	73 mm
Flute length L_c	16 mm
Direction of infeed	horizontal, oblique and vertical
Shank	DIN 6535 HB to h6

Tolerance nominal \varnothing	f8
Helix angle	38 degrees
Corner chamfer angle	45 degrees
Series	Master Steel
Coating	TiAlN
Tool material	Solid carbide
Standard	DIN 6527
Type	N
Helix angle characteristic	unequal spacing
Spacing of the cutters	unequal spacing
Cutting width a_e for milling operation	0.5×D for side milling
Cutting width a_e for milling operation	Full slot cutting depth 1×D
Through-coolant	no
Machining strategy	HPC
Colour ring	green
Type of product	End / face mill

User data

	Suitability	V_c	ISO code
Steel < 500 N/mm ²	suitable	260 m/min	P
Steel < 750 N/mm ²	suitable	240 m/min	P
Steel < 900 N/mm ²	suitable	190 m/min	P
Steel < 1100 N/mm ²	suitable	180 m/min	P
Steel < 1400 N/mm ²	suitable only under restricted conditions	150 m/min	P
INOX < 900 N/mm ²	suitable	80 m/min	M
INOX > 900 N/mm ²	suitable	70 m/min	M
GG(G)	suitable	250 m/min	K
Uni	suitable		

wet maximum	suitable
wet minimum	suitable only under restricted conditions
dry	suitable
Air	suitable