

Garant

**Side lock arbors Form ADB with cooling channel bore, BT 50 A = 100,
Clamping range \varnothing D1: 10mm**


Order data

| | |
|--------------|---------------|
| Order number | 302655 10 |
| GTIN | 4062406100162 |
| Item class | 31A |

Description
Version:

All shanks hard turned (for smooth running). Balancing quality G2.5 / 25,000 rpm. **With coolant supply holes that can be plugged.**

Application:

For clamping tools with side flats to DIN 1835 B and DIN 6535 HB.

Optional extras:

Pull studs (PS) No. 308760 – 308802. Pull stud wrenches No. 308820; 308835.

Technical description

| | |
|---------------------------------------|---------------|
| Spare clamping screw No. 30 9900 | 10 |
| Overhang dimension A | 100 mm |
| Clamping \varnothing D ₁ | 10 mm |
| External \varnothing D | 35 mm |
| Adapter | BT 50 A = 100 |
| Standard | DIN 6359 |
| Arbor standard | ISO 7388-2 |
| Arbor standard | JIS B6339 |

| | |
|---------------------------------------|---------------------|
| Shape | ADB |
| Balance quality G at rotational speed | G 2.5 at 25,000 rpm |
| Concentricity | ≤ 3 μm |
| Machining strategy | HPC |
| Type of product | Side lock arbor |

Accessories

| | |
|---|-----------|
| Pull stud 60°sealed suitable for steep tapers 50 | 308785 50 |
| Pull stud 45°sealed suitable for steep tapers 50 | 308760 50 |
| Wrench for pull studsDIN ISO 7388-1 (formerly DIN 69872) suitable for ISO taper size 50 | 308820 50 |
| Pull stud 90°sealed suitable for steep tapers 50 | 308790 50 |
| Pull stud 90°sealed suitable for steep tapers 50 | 308795 50 |
| Pull stud 45°sealed suitable for steep tapers 50 | 308765 50 |
| Wrench for pull studsISO 7388 suitable for ISO taper size 50 | 308830 50 |
| Spare clamping screw for chucks with clamping Ø D1 10 mm | 309900 10 |