

Garant

**Side lock arbors Form ADB with cooling channel bore, BT 50 A = 100,
Clamping range \varnothing D1: 12mm**


Order data

Order number	302655 12
GTIN	4062406100179
Item class	31A

Description
Version:

All shanks hard turned (for smooth running). Balancing quality G2.5 / 25,000 rpm. **With coolant supply holes that can be plugged.**

Application:

For clamping tools with side flats to DIN 1835 B and DIN 6535 HB.

Optional extras:

Pull studs (PS) No. 308760 – 308802. Pull stud wrenches No. 308820; 308835.

Technical description

Overhang dimension A	100 mm
Clamping \varnothing D ₁	12 mm
External \varnothing D	42 mm
Spare clamping screw No. 30 9900	12
Adapter	BT 50 A = 100
Standard	DIN 6359
Arbor standard	ISO 7388-2
Arbor standard	JIS B6339

Shape	ADB
Balance quality G at rotational speed	G 2.5 at 25,000 rpm
Concentricity	≤ 3 μm
Machining strategy	HPC
Type of product	Side lock arbor

Accessories

Pull stud 60°sealed suitable for steep tapers 50	308785 50
Pull stud 45°sealed suitable for steep tapers 50	308765 50
Pull stud 90°sealed suitable for steep tapers 50	308795 50
Wrench for pull studsDIN ISO 7388-1 (formerly DIN 69872) suitable for ISO taper size 50	308820 50
Pull stud 90°sealed suitable for steep tapers 50	308790 50
Pull stud 45°sealed suitable for steep tapers 50	308760 50
Wrench for pull studsISO 7388 suitable for ISO taper size 50	308830 50
Spare clamping screw for chucks with clamping Ø D1 12 mm	309900 12