



Side lock arbors Form AD, BT 30 short, Clamping range $\varnothing D_1$: 12mm



Order data

| | |
|--------------|---------------|
| Order number | 302597 12 |
| GTIN | 4062406100094 |
| Item class | 32A |

Description

Version:

All shanks fine bead blasted. Balancing quality G6.3 / 18,000 rpm.

Application:

For clamping tools with side flats to DIN 1835 B and DIN 6535 HB.

Optional extras:

Pull studs (PS) No. 308760 – 308802. Pull stud wrenches No. 308820; 308835.

Technical description

| | |
|---------------------------------------|---------------------|
| Spare clamping screw No. 30 9900 | 12 |
| External $\varnothing D$ | 42 mm |
| Overhang dimension A | 55 mm |
| Clamping $\varnothing D_1$ | 12 mm |
| Adapter | BT 30 short |
| Standard | DIN 6359 |
| Arbor standard | ISO 7388-2 |
| Arbor standard | JIS B6339 |
| Shape | AD |
| Balance quality G at rotational speed | G 6.3 at 18,000 rpm |

| | |
|--------------------|-----------------|
| Concentricity | ≤ 3 µm |
| Machining strategy | HPC |
| Type of product | Side lock arbor |

Accessories

| | |
|--|-----------|
| Pull stud 45°sealed suitable for steep tapers 30 | 308765 30 |
| Pull stud 45°sealed suitable for steep tapers 30 | 308760 30 |
| Pull stud 60°sealed suitable for steep tapers 30 | 308785 30 |
| Spare clamping screw for chucks with clamping Ø D1 12 mm | 309900 12 |