



ER collet chuck Form AD, BT 30 A = 60, for ER collet size: 16



Order data

Order number	302747 16
GTIN	4062406100988
Item class	32A

Description

Version:

External and internal taper ground.

- **All shanks fine bead blasted. Balancing quality G6.3 / 18,000 rpm.**
- **High-quality precision clamping nut.**

Application:

For clamping tools with parallel shank in collets to **DIN 6499 Form A and B.**

Supplied with:

ER clamping nut.

Optional extras:

ER collets No. 308881 – 309434, ER chuck keys No. 309680 – 309745 or No. 613300.

Pull studs (PS) No. 308760 – 308806. Pull stud wrenches No. 308820; 308835.

Note:

Matching clamping nut No. 309580 or 309610.

Machining strategy: HSC

Clamping range: 0.5 - 10 mm

External Ø D: 28 mm

Spare ER clamping nut: 16

ER chuck key: 16

Technical description

Clamping range	0.5 - 10 mm
Spare ER clamping nut	16

External Ø D	28 mm
ER chuck key	16
Adapter	BT 30 A = 60
Arbor standard	JIS B6339
Arbor standard	JIS B6339
Concentricity	≤ 3 µm
Machining strategy	HSC
Type of product	Collet chuck