



ER collet chuck Form AD, BT 40 short, for ER collet size: 16



Order data

Order number	302757 16
GTIN	4062406101015
Item class	32A

Description

Version:

External and internal taper ground.

- **All shanks fine bead blasted. Balancing quality G6.3 / 18,000 rpm.**
- **High-quality precision clamping nut.**

Application:

For clamping tools with parallel shank in collets to **DIN 6499 Form A and B.**

Supplied with:

ER clamping nut.

Optional extras:

ER collets No. 308881 – 309434, ER chuck keys No. 309680 – 309745 or No. 613300.

Pull studs (PS) No. 308760 – 308806. Pull stud wrenches No. 308820; 308835.

Note:

Matching clamping nut No. 309580 or 309610.

Machining strategy: HSC

Clamping range: 0.5 - 10 mm

Overhang dimension A: 70 mm

External Ø D: 28 mm

Spare ER clamping nut: 16

ER chuck key: 16

Technical description

Spare ER clamping nut	16
-----------------------	----

Clamping range	0.5 - 10 mm
External Ø D	28 mm
Overhang dimension A	70 mm
ER chuck key	16
Adapter	BT 40 short
Arbor standard	JIS B6339
Arbor standard	JIS B6339
Shape	AD
Balance quality G at rotational speed	G 6.3 at 18,000 rpm
Concentricity	≤ 3 µm
Machining strategy	HSC
Type of product	Collet chuck

Accessories

ER collet Nominal clamping Ø d 6 mm	308901 6
ER collet with seal Nominal clamping Ø d 3 mm	308921 3
Pull stud 60° sealed suitable for steep tapers 40	308785 40
Torque insert for Pull studs to SO 7388 suitable for ISO taper size 40	308812 40
ET collet with radial compensation for tapping and reaming Nominal clamping Ø d 2,8 mm	309445 2,8
Pull stud Hurco 45° with fit sealed suitable for steep tapers 40	308802 40
ER collet for machine taps with seal Nominal clamping Ø d 4,5 mm	309402 4,5
ER collet with seal Nominal clamping Ø d 6 mm	308921 6
Wrench for pull studs ISO 7388 suitable for ISO taper size 40	308830 40
ER collet Nominal clamping Ø d 8 mm	308901 8

ET collet for thread tapping, with axial compensation Nominal clamping Ø d 4,5 mm	309425 4,5
ET collet with radial compensation for tapping and reaming Nominal clamping Ø d 3,5 mm	309445 3,5
ER collet Nominal clamping Ø d 10 mm	308901 10
ER collet for machine taps with seal Nominal clamping Ø d 8 mm	309403 8
ER collet Nominal clamping Ø d 3 mm	308901 3
ER collet for machine taps with seal and spray nozzles Nominal clamping Ø d 7 mm	309404 7
Pull stud 45° sealed suitable for steep tapers 40	308760 40
Pull stud 90° sealed suitable for steep tapers 40	308790 40
ER plain bearing clamping nut for ER 16	309612 16
ET collet for thread tapping, with axial compensation Nominal clamping Ø d 3,5 mm	309425 3,5
ER collet with seal Nominal clamping Ø d 10 mm	308921 10
ER collet for machine taps with seal and spray nozzles Nominal clamping Ø d 4,5 mm	309404 4,5
ER collet for machine taps with seal Nominal clamping Ø d 6 mm	309402 6
ER collet Nominal clamping Ø d 3 mm	308920 3
Hurco 60° pull stud with bore and fit sealed suitable for steep tapers 40	308803 40
ER collet with seal and spray nozzles Nominal clamping Ø d 4 mm	308922 4
Pull stud 45° sealed suitable for steep tapers 40	308765 40
Pull stud Hurco 60° with fit sealed suitable for steep tapers 40	308804 40
ER collet with seal Nominal clamping Ø d 5 mm	308906 5
ER collet with seal Nominal clamping Ø d 4 mm	308906 4
ER collet with seal and spray nozzles Nominal clamping Ø d 5 mm	308922 5
	309402 3,5

ER collet for machine taps with seal Nominal clamping Ø d 3,5 mm	
ER collet for machine taps with seal Nominal clamping Ø d 3,5 mm	309403 3,5
ER collet with seal Nominal clamping Ø d 10 mm	308906 10
ER collet Nominal clamping Ø d 4 mm	308901 4
Pull stud Hurco 90° with bore and fit sealed suitable for steep tapers 40	308805 40
ER collet Nominal clamping Ø d 5 mm	308920 5
ET collet with radial compensation for tapping and reaming Nominal clamping Ø d 4,5 mm	309445 4,5
ER collet with seal and spray nozzles Nominal clamping Ø d 7 mm	308922 7
ER collet with seal Nominal clamping Ø d 4 mm	308921 4
ER collet Nominal clamping Ø d 7 mm	308920 7
ER collet for machine taps with seal and spray nozzles Nominal clamping Ø d 6 mm	309404 6
Pull stud Hurco 90° with fit sealed suitable for steep tapers 40	308806 40
ER collet for machine taps with seal Nominal clamping Ø d 8 mm	309402 8
ER collet with seal Nominal clamping Ø d 9 mm	308906 9
ER collet for machine taps with seal Nominal clamping Ø d 2,8 mm	309402 2,8
ET collet with radial compensation for tapping and reaming Nominal clamping Ø d 6 mm	309445 6
ER collet Nominal clamping Ø d 9 mm	308901 9
ER collet with seal Nominal clamping Ø d 8 mm	308906 8
ER collet for machine taps with seal Nominal clamping Ø d 4 mm	309402 4
ER collet Nominal clamping Ø d 2 mm	308901 2
ER collet for machine taps with seal Nominal clamping Ø d 4,5 mm	309403 4,5

ER collet with seal Nominal clamping Ø d 8 mm	308921 8
Torque insert for Pull studs to DIN 69872 suitable for ISO taper size 40	308810 40
ER collet Nominal clamping Ø d 10 mm	308920 10
ET collet for thread tapping, with axial compensation Nominal clamping Ø d 2,8 mm	309425 2,8
ER collet for machine taps with seal Nominal clamping Ø d 4 mm	309403 4
ER collet for machine taps with seal Nominal clamping Ø d 7 mm	309403 7
ER collet Nominal clamping Ø d 2 mm	308920 2
ER clamping nut for ER 16	309580 16
ER collet with seal Nominal clamping Ø d 5 mm	308921 5
ET collet for thread tapping, with axial compensation Nominal clamping Ø d 6 mm	309425 6
Pull-stud 60° sealed suitable for steep tapers 40	308780 40
ER collet Nominal clamping Ø d 2,5 mm	308901 2,5
ER collet for machine taps with seal Nominal clamping Ø d 2,8 mm	309403 2,8
ER collet with seal Nominal clamping Ø d 6 mm	308906 6
ER collet with seal Nominal clamping Ø d 7 mm	308906 7
ER collet Nominal clamping Ø d 6 mm	308920 6
ER collet Nominal clamping Ø d 1,5 mm	308901 1,5
ET collet with radial compensation for tapping and reaming Nominal clamping Ø d 3 mm	309445 3
ER collet with seal and spray nozzles Nominal clamping Ø d 10 mm	308922 10
ET collet with radial compensation for tapping and reaming Nominal clamping Ø d 5 mm	309445 5
ER collet Nominal clamping Ø d 9 mm	308920 9
ER collet Nominal clamping Ø d 7 mm	308901 7
ER collet Nominal clamping Ø d 4 mm	308920 4

ER clamping nut for HiRunER collet chucks for ER 16	309617 16
ER collet with seal and spray nozzles Nominal clamping Ø d 3 mm	308922 3
ER collet with seal and spray nozzles Nominal clamping Ø d 8 mm	308922 8
ER collet Nominal clamping Ø d 8 mm	308920 8
ER collet with seal Nominal clamping Ø d 9 mm	308921 9
Wrench for pull studs DIN ISO 7388-1 (formerly DIN 69872) suitable for ISO taper size 40	308820 40
ER collet with seal Nominal clamping Ø d 7 mm	308921 7
ER collet for machine taps with seal and spray nozzles Nominal clamping Ø d 3,5 mm	309404 3,5
ER collet Nominal clamping Ø d 1 mm	308901 1
ET collet with radial compensation for tapping and reaming Nominal clamping Ø d 2 mm	309445 2
ET collet with radial compensation for tapping and reaming Nominal clamping Ø d 4 mm	309445 4
ER collet with seal and spray nozzles Nominal clamping Ø d 6 mm	308922 6
ER collet with seal Nominal clamping Ø d 3 mm	308906 3
Pull stud 90° sealed suitable for steep tapers 40	308795 40
ER collet Nominal clamping Ø d 5 mm	308901 5
ER collet for machine taps with seal Nominal clamping Ø d 7 mm	309402 7
ER collet with seal and spray nozzles Nominal clamping Ø d 9 mm	308922 9
ER collet Nominal clamping Ø d 1 mm	308920 1
Pull stud Hurco 45° with bore and fit sealed suitable for steep tapers 40	308801 40
ER collet for machine taps with seal and spray nozzles Nominal clamping Ø d 8 mm	309404 8
ER collet for machine taps with seal Nominal clamping Ø d 9 mm	309402 9

ER collet for machine taps with seal Nominal clamping \varnothing d 6 mm	309403 6
Single open ended spanner Width across flats 25 mm	613300 25
ER collet for machine taps with seal Nominal clamping \varnothing d 9 mm	309403 9
ER clamping nut High Speed for ER 16	309610 16