



Face mill arbor Form A, BT 30 short, Spigot \varnothing d1: 22mm



Order data

Order number	303007 22
GTIN	4062406101176
Item class	32A

Description

Version:

Taper shank, spigots, and contact surfaces ground on collar.
All shanks fine bead blasted. Balancing quality G6.3 / 18,000 rpm. Form A.

Supplied with:

Lock screw.

Optional extras:

Pull studs (PS) No. 308760 – 308802. Special toggle spanner No. 309840.

Technical description

Spigot \varnothing d ₁	22 mm
Overhang dimension A	40 mm
External \varnothing D	48 mm
Suitable toggle spanner No. 309840	22
Spare milling cutter lock screw No. 309860 / 309861	22
Clamping \varnothing D ₁	22 mm
Adapter	BT 30 short
Standard	DIN 6357
Arbor standard	JIS B6339

Arbor standard	ISO 7388-2
Shape	A
Balance quality G at rotational speed	G 6.3 at 18,000 rpm
Concentricity	$\leq 5 \mu\text{m}$
Machining strategy	HPC
Type of product	Milling head arbor