

**Garant**
**GARANT Master Steel solid carbide roughing end mill HPC, TiAlN, Ø f8 DC: 4mm**

**Order data**

Order number	203035 4
GTIN	4045197718747
Item class	11X

**Description**
**Version:**

For **roughing and finishing**.

Up to 1.5×D into solid material **at very high feed rates** with smooth cutting action.

**Advantage:**

Optimised flute form, eccentric relief ground, wide chip space.

**Technical description**

Feed $f_z$ for slot milling in steel < 900 N/mm <sup>2</sup>	0.02 mm
No. of teeth Z	4
Feed $f_z$ for side milling in steel < 900 N/mm <sup>2</sup>	0.025 mm
Corner chamfer width at 45°	0.08 mm
Cutting edge Ø D <sub>c</sub>	4 mm
Shank Ø D <sub>s</sub>	6 mm
Overall length L	57 mm
Flute length L <sub>c</sub>	11 mm
Direction of infeed	horizontal, oblique and vertical
Shank	DIN 6535 HB to h6
Tolerance nominal Ø	f8
Helix angle	38 degrees

Corner chamfer angle	45 degrees
Series	Master Steel
Coating	TiAlN
Tool material	Solid carbide
Standard	DIN 6527
Type	N
Helix angle characteristic	unequal spacing
Spacing of the cutters	unequal spacing
Cutting width $a_e$ for milling operation	0.3×D for side milling
Cutting width $a_e$ for milling operation	Full slot cutting depth 1×D
Through-coolant	no
Machining strategy	HPC
Colour ring	green
Type of product	End / face mill

## User data

	Suitability	$V_c$	ISO code
Steel < 500 N/mm <sup>2</sup>	suitable	260 m/min	P
Steel < 750 N/mm <sup>2</sup>	suitable	240 m/min	P
Steel < 900 N/mm <sup>2</sup>	suitable	190 m/min	P
Steel < 1100 N/mm <sup>2</sup>	suitable	180 m/min	P
Steel < 1400 N/mm <sup>2</sup>	suitable only under restricted conditions	150 m/min	P
INOX < 900 N/mm <sup>2</sup>	suitable	80 m/min	M
INOX > 900 N/mm <sup>2</sup>	suitable	70 m/min	M
GG(G)	suitable	250 m/min	K
Uni	suitable		
wet maximum	suitable		

wet minimum	suitable only under restricted conditions
dry	suitable
Air	suitable