

**CoolSpeed®****High-speed spindle housing, Type: TBL****Order data**

Order number	319991 TBL
GTIN	2050001960696
Item class	36D

**Description****Version:**

High-speed spindle, driven by coolant (10 – 60 bar), speeds up to 75,000 rpm.

**Application:**

Increased feed rate and cutting speed, for use above all with small-diameter tools (shank  $\varnothing$  3 – 6 mm). For use for drilling, deburring, engraving, and milling to a restricted degree.

**Technical description**

$L_2$	48 mm
$\varnothing D_2$	30 mm
$L_3$	80 mm
External $\varnothing D$	16 mm
External $\varnothing D_1$	25 mm
Shank length $L_1$	13.5 mm
Type of product	High-speed spindle