

Garant GRIDLINE

Workbench, mobile, with electric height adjustment, cable, left side cupboard, right side 4 drawers, Bamboo worktop, 20×20G, Worktop length: 1500/DEmm**Order data**

Order number	924511 1500/DE
GTIN	4062406101831
Item class	9GG

Description**Version:**

Workbench in sturdy steel construction with frame of rectangular hollow section. **100% full extension drawers** with differential runners, single-handed individual drawer release system and 75 kg load capacity. Drawer casing 24G can be locked centrally with cylinder lock.

Stepless electric drive for height adjustment. Height adjustment by pushbutton.

With 2 each ball-bearing fixed wheels and castors, Ø 125 mm, with **treadless polyurethane tyres**, minimum rolling resistance, low noise and fibre shields. Castors with brakes for the wheels and the castor heads.

Connecting cable length 8 m. With plug type F.

Function:

IP20: Protected against penetration by foreign bodies with $\varnothing < 12$ mm, however touching should be avoided, and offers no protection against water.

Fitted with:

Door height (left) mm: 525

Drawer front height (right): 1

Drawer front height (right) mm: 75, 100, 150, 200

Colour:

Cabinet body and drawer body RAL 7035 light grey, drawer fronts and cupboard doors RAL 7016 anthracite, **powder-coated. Drawer body not configurable, always RAL 7035 light grey.**

Technical description

Castor Ø	125 mm
Drawer usable width	500 mm
Fixed wheel Ø	125 mm
Stepless height adjustment	yes
Number of drawers	4
Worktop thickness	50 mm
Worktop length	1500 mm
Material of wheel	Polyurethan
Treadless tyres	yes
Supply voltage	250 V
ComfortClose	no
Drawer usable area in G	20×20
Drawer usable depth in G	20
can be lowered	yes
Drawer usable depth	500 mm
Height adjustment range	850 - 1050 mm
Drawer body usable height	525 mm
Push handle	no
Series	Ready-to-go
Support cabinet depth	700 mm
Drawer usable width in G	20
Support cabinet width	1300 mm
Lifting speed	9 mm/s
Number of castors with parking brake	2
Number of fixed wheels without parking brake	2
Principle of height adjustment	electrical
Number of doors	1
Weight	172.9 kg
maximum lifting force	6000 N

Worktop depth	750 mm
Material of worktop	Bamboo
Individual drawer release system	One-hand
IP Index of Protection	IP 20
Power supply	Rechargeable battery-powered
Power supply	Mains operated
Nominal voltage	250 V
Plug type, input	F
Design version	Steel hollow section construction
Material thickness	1 mm
Height adjustment workstation	850-1050 mm
Drawer/pull-out shelf load capacity	75 kg
Workbench/desk load capacity - maximum distributed load (on wood)	400 kg
Type of height adjustment	electrical
Insert thickness	50 mm
Drawer runner extension (partial/full extension)	100 %
Door opening angle	180 degrees
Cylinder lock	modular lock barrel
Colour selection	RAL 9002, 7035, 7005, 7016, 6011, 5018, 5012, 5011, 5005, 3003
Product name attribute	20x20G
Type of product	mobile workbench

Accessories

Slide handle for GridLine Type KO12	914226 KO12
Lock plate for GridLine Type KO21	914227 KO21
Drawer with one-handed individual drawer release system Drawer front height 200 mm	927805 200

Drawer with one-handed individual drawer release system
Drawer front height 75 mm

927805 75

Drawer with one-handed individual drawer release system
Drawer front height 150 mm

927805 150

Drawer with one-handed individual drawer release system
Drawer front height 100 mm

927805 100