

Garant GRIDLINE

Workbench, self-propelled with electric drive, left side cupboard, right side 4 drawers, Beech marine ply worktop, 20×20G, Worktop length: 1250mm**Order data**

Order number	925424 1250
GTIN	4062406101909
Item class	9GG

Description**Version:**

Workbench in sturdy steel construction with frame of rectangular hollow section. Drawer casing 24G and cupboard casing 16G can be locked centrally with cylinder lock. **100% full extension drawers** with differential runners, single-handed individual drawer release system and 75 kg load capacity.

Power supply for the drive unit by the integral battery.

Drive unit: Maximum speed **4 km/h**, travel direction forwards and reverse, ground clearance 30 mm, rubber treadless wheels, mechanical emergency release, audible noise energy (drive) 45 dB(A).

With 2 each ball-bearing fixed wheels and castors, Ø 125 mm, with **treadless polyurethane tyres**, minimum rolling resistance, low noise and fibre shields. Castors with brakes for the wheels and the castor heads.

Function:

IPX4: Protected against splashed water from all directions, but without any protection against foreign bodies or touching.

Fitted with:

Door height (left) mm: 625

Number of height-adjustable shelves (left): 1

Drawer front height (right) mm: 75, 100, 200, 250

Colour:

Cabinet body and drawer body RAL 7035 light grey, drawer fronts and cupboard doors RAL 7016 anthracite, **powder-coated. Drawer body not configurable, always RAL 7035 light grey.**

Technical description

can be lowered	no
Material of worktop	Beech marine ply
Drawer usable depth in G	20
Number of drawers	4
Nominal voltage	24 V
Weight	171 kg
Drawer usable depth	500 mm
maximum lifting force	400 N
Castor Ø	125 mm
Worktop depth	750 mm
Drawer usable width	500 mm
ComfortClose	no
Push handle	yes
Number of castors with parking brake	2
Fixed wheel Ø	125 mm
Rated power	73 W
Support cabinet width	1100 mm
Number of fixed wheels without parking brake	2
Drawer body usable height	625 mm
Worktop length	1250 mm
Treadless tyres	yes
Worktop thickness	25 mm
Number of doors	1
Series	Ready-to-go
Height	950 mm
Support cabinet depth	700 mm
Drawer usable width in G	20

Drawer usable area in G	20×20
Individual drawer release system	One-hand
Type of rechargeable battery	Lithium-ion
IP Index of Protection	IP X4
Power supply	Rechargeable battery-powered
Power supply	Mains operated
Design version	Steel hollow section construction
Material thickness	1 mm
Workbench height	950 mm
Drawer/pull-out shelf load capacity	75 kg
Workbench/desk load capacity - maximum distributed load (on wood)	400 kg
Insert thickness	25 mm
Drawer runner extension (partial/full extension)	100 %
Door opening angle	180 degrees
Cylinder lock	modular lock barrel
Colour selection	RAL 9002, 7035, 7005, 7016, 6011, 5018, 5012, 5011, 5005, 3003
Product name attribute	20×20G
Type of product	mobile workbench

Accessories

Drawer with one-handed individual drawer release system Drawer front height 100 mm	927805 100
Slide handle for GridLine Type KO12	914226 KO12
Drawer with one-handed individual drawer release system Drawer front height 75 mm	927805 75
Lock plate for GridLine Type KO21	914227 KO21
	927805 200

Drawer with one-handed individual drawer release system
Drawer front height 200 mm

Drawer with one-handed individual drawer release system
Drawer front height 250 mm

927805 250