



ER clamping nut with radial run-out adjustment, for ER: 16



Order data

Order number	309619 16
GTIN	2050002004016
Item class	33E

Description

Version:

Thread and taper ground in a single setup for highest concentricity.
6 screws allow the radial run-out to be reduced to zero.

Suitable for:

All standard ER collet chucks.
Ideally suitable for lathes, both for stationary and driven tools.

Optional extras:

ER clamping wrench, No. 309680 – 309740.
Single open ended spanner (for size 16), No. 613300 size 25.

Note:

Collet chuck and clamping nut are balanced separately!
Up to 6000 rpm.

Technical description

for ER	16 mm
External \varnothing D	34 mm

Overall length L	21 mm
Thread	M22×1.5
Standard	DIN 6499 D
Type of product	Clamping nut