



ER clamping nut with radial run-out adjustment, for ER: 40



Order data

Order number	309619 40
GTIN	2050002004047
Item class	33E

Description

Version:

Thread and taper ground in a single setup for highest concentricity.
6 screws allow the radial run-out to be reduced to zero. **With slots.**

Suitable for:

All standard ER collet chucks.

Ideally suitable for lathes, both for stationary and driven tools.

Optional extras:

ER clamping wrench, No. 309680 – 309740.

Single open ended spanner (for size 16), No. 613300 size 25.

Note:

Collet chuck and clamping nut are balanced separately!
Up to 6000 rpm.

Technical description

Overall length L	27.5 mm
External \varnothing D	78 mm

for ER	40 mm
Thread	M50×1.5
Standard	DIN 6499 D
Type of product	Clamping nut