


Garant
Milling insert Ø 16 mm stub conical, Type: HART

Order data

Order number	212776 HART
GTIN	4062406103170
Item class	21A

Description
Version:

Detailed application values can be found in the GARANT machining handbook No. 110020.

· **Radius, concentricity and interchange accuracy: ± 0.015 mm.**

Feed f_z in steel < 60 HRC: 0.08 mm

Grade: HB7705

Technical description

Type	HART
Grade	HB7705
Corner radius	1 mm
Tool material	Carbide
Axial length of wiper	16 mm
Radial length of wiper	32 mm
Corner radius R_1	1 mm
Flute length L_c	8 mm

Feed f_z in steel < 1400 N/mm ²	0.1 mm
Feed f_z in steel < 60 HRC	0.08 mm
Number of changes/inserts	1
Coating	TiN
Type of product	Indexable insert for milling