

**Garant**
**Synchro tool head for ER16, Tap shank  $\varnothing$  d<sub>2</sub>: 6mm**

**Order data**

Order number	338183 6
GTIN	4062406102074
Item class	31P

**Description**
**Version:**

- **Tapping and thread forming on machines with synchronised spindles.**
- **Minimum Length Adjustment: +0.5mm / -0.2 mm.**
- **Compensation for synchronisation errors, hence better thread quality and clear increase in tool life.**
- **For collet chucks and driven tools to ISO 15488 (DIN 6499).**
- **Suitable for left-hand and right-hand threads.**

**Suitable for:**

ER synchro collet No. 338180.

**Technical description**

Overhang L <sub>1</sub>	32 mm
Shank square	4.9 mm
for tap shank $\varnothing$ d <sub>2</sub> DIN 374/376	M8
for tap shank $\varnothing$ d <sub>2</sub> DIN 371	M5-6
$\varnothing$ D <sub>2</sub>	12.7 mm
Through-coolant	yes, with max. 50 bar
Type of product	Tapping adapter

