

Flat magnet with bore, Neodymium, Ø: 20mm**Order data**

Order number	085932 20
GTIN	5012095608486
Item class	08Q

Description**Version:**

- **Temperature-resistant up to maximum 80 °C.**
- **Galvanised surface, magnetic core made of neodymium.**
- **Shielded flat magnet with 3 to 6 times the clamping force compared to hard ferrite magnets.**

Application:

For clamping, assembling, incorporation by screw fastening.

Technical description

maximum temperature resistance	80 °C
Ø	20 mm
Height	6 mm
Bore Ø	4.5 mm
Nominal clamping force	105 N
Material of the magnet core	Neodymium
Type of product	Flat gripper magnet

