

Flat magnet with bore, Neodymium, Ø: 40mm**Order data**

| | |
|--------------|---------------|
| Order number | 085932 40 |
| GTIN | 5012095608516 |
| Item class | 08Q |

Description**Version:**

- **Temperature-resistant up to maximum 80 °C.**
- **Galvanised surface, magnetic core made of neodymium.**
- **Shielded flat magnet with 3 to 6 times the clamping force compared to hard ferrite magnets.**

Application:

For clamping, assembling, incorporation by screw fastening.

Technical description

| | |
|--------------------------------|---------------------|
| Height | 8 mm |
| Ø | 40 mm |
| Bore Ø | 5.5 mm |
| Nominal clamping force | 500 N |
| maximum temperature resistance | 80 °C |
| Material of the magnet core | Neodymium |
| Type of product | Flat gripper magnet |

