

**Garant****Synchro tool head for ER32, Tap shank  $\varnothing$  d2: 11 mm****Order data**

Order number	338186 11
GTIN	4062406103682
Item class	31P

**Description****Version:**

- **Tapping and thread forming on machines with synchronised spindles.**
- **Minimum Length Adjustment: +0.5mm / -0.2 mm.**
- **Compensation for synchronisation errors, hence better thread quality and clear increase in tool life.**
- **For collet chucks and driven tools to ISO 15488 (DIN 6499).**
- **Suitable for left-hand and right-hand threads.**

**Version of the advertising text:**

- **Minimum Length Adjustment: +0.5mm / -0.2 mm.**
- **Compensation for synchronisation errors, hence better thread quality and clear increase in tool life.**

**Suitable for:**

ER synchro collet No. 338180.

**Technical description**

Overhang $L_1$	37 mm
Shank square	9 mm
for tap shank $\varnothing$ d <sub>2</sub> DIN 374/376	M14
$\varnothing$ D <sub>2</sub>	25 mm
Through-coolant	yes, with max. 50 bar
Type of product	Tapping adapter

