

**Garant**
**Grooving toolholder, right-hand, Shank width / groove width w: 12/1,5mm**

**Order data**

Order number	273757 12/1,5
GTIN	4045197720160
Item class	21W

**Description**
**Version:**

Made of high-tensile tool steel ( $> 1300 \text{ N/mm}^2$ ). In conjunction with the convex insert clamping, the system achieves very high resistance to axial and radial cutting forces and thereby significantly increases the surface quality and productivity.

**Note:**

From 19.5 mm groove depth (up to groove width 3 mm) and from 24.5 mm groove depth (from groove width 4 mm) the second cutter comes into contact with the workpiece. This can lead to scoring. If necessary, use single-ended grooving inserts No. 273656 – 273670.

**Technical description**

Screw	279815 4 (TX15; 3.5 Nm)
Grooving depth $t_{\max}$	10.5 mm
Head length $L_1$	28.5 mm
Functional width $L_4$	12 mm
Groove width w	1.5 mm
Overall length L	150 mm
Shank width b	12 mm
Application type	right-hand
Through-coolant	no
axial grooving possible	yes

Type of product

Boring bar

---

**Accessories**

PrecisionBit for Torx®, 1/4 inch E 6.3 Torx® profile TX15

674248 TX15

Clamping screw Type 4

279815 4

Torque screwdriver with scale, to take interchangeable blades maximum torque 500 cNm

659957 500