

Garant**Intermediate sleeve, SK 50, Short taper SK / SK 1: 50/50****Order data**

Order number	301273 50/50
GTIN	4062406105129
Item class	31A

Description**Supplied with:**

With built-in connecting screw for arbors according to ISO 7388-1. (Formerly DIN 69871)

Optional extras:

Pull studs (PS) No. 308600 – 308806. Pull stud wrenches No. 308820; 308835.

Technical description

External \varnothing D	97 mm
Overhang dimension A	120 mm
Adapter	SK 50
Arbor standard	ISO 7388-1
Shape	A
Balance quality G at rotational speed	G 2.5 at 15,000 rpm
Concentricity	$\leq 5 \mu\text{m}$
Type of product	Intermediate sleeve

Accessories

Wrench for pull studsISO 7388 suitable for ISO taper size 50	308830 50
Pull stud, 18CrNiMo7Form A suitable for steep tapers 50	308605 50
Pull stud 45°sealed suitable for steep tapers 50	308765 50
Pull studForm A suitable for steep tapers 50	308600 50
Pull studForm B suitable for steep tapers 50	308640 50
Pull stud 90°sealed suitable for steep tapers 50	308790 50
Pull studsealed, form B suitable for steep tapers 50	308620 50
Pull stud 90°sealed suitable for steep tapers 50	308795 50
Special pull stud with no internal threadsealed suitable for steep tapers 50	308720 50
Pull studsealed suitable for steep tapers 50	308660 50
Pull studsealed, form A suitable for steep tapers 50	308610 50
Torque wrenchwith reversible ratchet maximum torque 200 N·m	656050 200
Special pull stud with internal thread suitable for steep tapers 50	308740 50
Pull stud 45°sealed suitable for steep tapers 50	308760 50
Pull stud 60°sealed suitable for steep tapers 50	308785 50
Pull stud, 18CrNiMo7sealed, form B suitable for steep tapers 50	308615 50
Wrench for pull studsDIN ISO 7388-1 (formerly DIN 69872) suitable for ISO taper size 50	308820 50
Pull studsealed, form B suitable for steep tapers 50	308650 50