

Garant
**Arbor for screw-in milling cutters with thread, SK 40, Thread M × Length L1:
M8X100**

Order data

Order number	301303 M8X100
GTIN	4062406105358
Item class	31A

Description
Version:

Tapered design.

Application:

To take screw-in milling cutters with thread.

Optional extras:

Pull studs (PS) No. 308600 – 308806, PS wrenches No. 308820 – 308835.

Machining strategy: HSC

Overhang dimension A: 119 mm

Bore $\varnothing D_1$ tolerance IT6: 8.5 mm

$\varnothing D_2$: 13 mm

External $\varnothing D$: 25 mm

Reach L_1 : 100 mm

L_2 : 5 mm

Technical description

External $\varnothing D$	25 mm
Thread M	M8×100
Overhang dimension A	119 mm
Bore $\varnothing D_1$ tolerance IT6	8.5 mm
L_2	5 mm

Reach L ₁	100 mm
Ø D ₂	13 mm
Adapter	SK 40
Arbor standard	ISO 7388-1
Shape	ADB
Balance quality G at rotational speed	G 2.5 at 25,000 rpm
Concentricity	≤ 3 µm
Machining strategy	HSC
Type of product	Threaded copy mill arbor

Accessories

Pull stud Mori-Seiki, sealed, form A suitable for steep tapers 40	308630 40
Special pull stud with no internal thread sealed suitable for steep tapers 40	308700 40
Pull stud Mori-Seiki, sealed, form A suitable for steep tapers 40	308625 40
Torque insert for Pull studs to DIN 69872 suitable for ISO taper size 40	308810 40
Pull stud sealed, form B suitable for steep tapers 40	308620 40
Special pull stud with internal thread suitable for steep tapers 40	308740 40
Pull stud, 18CrNiMo7 Form A suitable for steep tapers 40	308605 40
Pull stud sealed suitable for steep tapers 40	308660 40
Special pull stud with no internal thread sealed suitable for steep tapers 40	308720 40
ER chuck key 1/2 inch socket for ER collet chuck 40	309700 40
Torque insert for Pull studs to SO 7388 suitable for ISO taper size 40	308812 40
Pull stud Form B suitable for steep tapers 40	308640 40

Wrench for pull studs DIN ISO 7388-1 (formerly DIN 69872) suitable for ISO taper size 40	308820 40
Pull stud 45° sealed suitable for steep tapers 40	308760 40
Pull stud Mazak, form A suitable for steep tapers 40M	308670 40M
Pull stud 60° sealed suitable for steep tapers 40	308785 40
Torque wrench with reversible ratchet maximum torque 200 N·m	656050 200
Hurco 45° pull stud with 4-mm bore and fit sealed suitable for steep tapers 40	308801 40
ER chuck key for ER collet chuck 40	309680 40
Pull stud Hurco 45° with fit sealed suitable for steep tapers 40	308802 40
Pull stud 45° sealed suitable for steep tapers 40	308765 40
Pull stud 90° sealed suitable for steep tapers 40	308790 40
Wrench for pull studs ISO 7388 suitable for ISO taper size 40	308830 40
Pull stud Hurco 90° with fit sealed suitable for steep tapers 40	308806 40
Pull stud 90° sealed suitable for steep tapers 40	308795 40
Pull stud sealed, form B suitable for steep tapers 40	308650 40
Pull stud Form A suitable for steep tapers 40	308600 40
Pull stud, 18CrNiMo7 sealed, form B suitable for steep tapers 40	308615 40
Pull stud sealed, form A suitable for steep tapers 40	308610 40
Pull stud sealed suitable for steep tapers 40	308635 40