



Base body 6371G-50-500-040 MT shank, with through-coolant, 1.5×D, Type: 12



Order data

Order number	232271 12
GTIN	4062406104504
Item class	22G

Description

Version:

With internal cooling.

Straight fluted.

Note:

Further sizes available on request.

For suitable reducing adapters for tools with MT shanks see **No. 343000-343530**.

Through-coolant: yes

Number of cutting edges Z: 2

Dia. range D_c : 12 - 12.5 mm

Reach L_1 : 18.8 mm

Morse taper MT size: 2

Clamping screws: 232990 TX7

Technical description

Clamping screws	232990 TX7
Morse taper MT size	2
Dia. range D_c	12 - 12.5 mm
Reach L_1	18.8 mm
Number of cutting edges Z	2
Version	1.5×D
Shank	Morse taper

Through-coolant	yes
Type of product	Indexable drill