



Base body MT shank, with through-coolant, 12×D, Type: 48



Order data

Order number	232275 48
GTIN	4062406106096
Item class	22G

Description

Version:

For holes up to IT10 accuracy.

With internal cooling. **Straight fluted.**

Note:

For suitable reducing adapters for tools with MT shanks see **No. 343000-343530**.

Further sizes available on request.

Reduce feed rates f by 10% and v_c values by 30%.

Technical description

Morse taper MT size	5
Clamping screws	232990 TX20
Dia. range D_c	48 - 65 mm
Reach L_1	576 mm
Number of cutting edges Z	2
Version	12×D
Shank	Morse taper
Through-coolant	yes
Type of product	Indexable drill