

**Garant****Arbor for screw-in milling cutters with thread, SK 50, Thread M × Length L1:  
M10X150****Order data**

Order number	301304 M10X150
GTIN	4062406105570
Item class	31A

**Description****Version:**

Tapered design.

**Application:**

To take screw-in milling cutters with thread.

**Optional extras:**

Pull studs (PS) No. 308600 – 308806, PS wrenches No. 308820 – 308835.

**Technical description**

Reach L <sub>1</sub>	150 mm
L <sub>2</sub>	10 mm
Thread M	M10×150
Ø D <sub>2</sub>	18 mm
Overhang dimension A	169 mm
External Ø D	36.5 mm
Bore Ø D <sub>1</sub> tolerance IT6	10.5 mm
Adapter	SK 50
Arbor standard	ISO 7388-1

Shape	ADB
Balance quality G at rotational speed	G 2.5 at 25,000 rpm
Concentricity	≤ 3 μm
Machining strategy	HSC
Type of product	Threaded copy mill arbor

## Accessories

Pull studsealed, form A suitable for steep tapers 50	308610 50
Pull studForm A suitable for steep tapers 50	308600 50
Pull stud 60°sealed suitable for steep tapers 50	308785 50
Pull stud 45°sealed suitable for steep tapers 50	308760 50
Torque wrenchwith reversible ratchet maximum torque 200 N·m	656050 200
Pull stud, 18CrNiMo7sealed, form B suitable for steep tapers 50	308615 50
Pull stud 90°sealed suitable for steep tapers 50	308790 50
Pull studsealed suitable for steep tapers 50	308660 50
Pull stud 45°sealed suitable for steep tapers 50	308765 50
Pull studsealed, form B suitable for steep tapers 50	308620 50
Special pull stud with no internal threadsealed suitable for steep tapers 50	308720 50
Wrench for pull studsDIN ISO 7388-1 (formerly DIN 69872) suitable for ISO taper size 50	308820 50
Pull studsealed, form B suitable for steep tapers 50	308650 50
Special pull stud with internal thread suitable for steep tapers 50	308740 50
Pull studForm B suitable for steep tapers 50	308640 50
Pull stud, 18CrNiMo7Form A suitable for steep tapers 50	308605 50
Pull stud 90°sealed suitable for steep tapers 50	308795 50

Wrench for pull studs ISO 7388 suitable for ISO taper size 50

308830 50