

**Garant**
**Arbor for screw-in milling cutters with thread, SK 40, Thread M × Length L1: M16X75**

**Order data**

Order number	301303 M16X75
GTIN	4062406105518
Item class	31A

**Description**
**Version:**

Tapered design.

**Application:**

To take screw-in milling cutters with thread.

**Optional extras:**

Pull studs (PS) No. 308600 – 308806, PS wrenches No. 308820 – 308835.

**Technical description**

Bore $\varnothing D_1$ tolerance IT6	17 mm
$\varnothing D_2$	29 mm
$L_2$	5 mm
Overhang dimension A	94 mm
Thread M	M16×75
External $\varnothing D$	34 mm
Reach $L_1$	75 mm
Adapter	SK 40
Arbor standard	ISO 7388-1
Shape	ADB

Balance quality G at rotational speed	G 2.5 at 25,000 rpm
Concentricity	≤ 3 μm
Machining strategy	HSC
Type of product	Threaded copy mill arbor

## Accessories

Pull studMori-Seiki, sealed, form A suitable for steep tapers 40	308630 40
Pull stud 90°sealed suitable for steep tapers 40	308790 40
Wrench for pull studsISO 7388 suitable for ISO taper size 40	308830 40
Pull studsealed, form B suitable for steep tapers 40	308650 40
Pull studForm B suitable for steep tapers 40	308640 40
Pull stud Hurco 45° with fitsealed suitable for steep tapers 40	308802 40
Special pull stud with no internal threadsealed suitable for steep tapers 40	308700 40
Pull studForm A suitable for steep tapers 40	308600 40
Pull stud, 18CrNiMo7Form A suitable for steep tapers 40	308605 40
Pull studsealed suitable for steep tapers 40	308660 40
Torque wrenchwith reversible ratchet maximum torque 200 N·m	656050 200
Pull stud 45°sealed suitable for steep tapers 40	308765 40
Pull stud Hurco 90° with fitsealed suitable for steep tapers 40	308806 40
Pull studsealed, form B suitable for steep tapers 40	308620 40
Pull studMori-Seiki, sealed, form A suitable for steep tapers 40	308625 40
Pull stud 45°sealed suitable for steep tapers 40	308760 40
Pull stud 60°sealed suitable for steep tapers 40	308785 40
Pull studsealed suitable for steep tapers 40	308635 40

Wrench for pull studs DIN ISO 7388-1 (formerly DIN 69872) suitable for ISO taper size 40	308820 40
ER chuck key for ER collet chuck 40	309680 40
Hurco 45° pull stud with 4-mm bore and fitsealed suitable for steep tapers 40	308801 40
Pull stud sealed, form A suitable for steep tapers 40	308610 40
Special pull stud with internal thread suitable for steep tapers 40	308740 40
Pull stud 90° sealed suitable for steep tapers 40	308795 40
Pull stud, 18CrNiMo7 sealed, form B suitable for steep tapers 40	308615 40
Pull stud Mazak, form A suitable for steep tapers 40M	308670 40M
ER chuck key 1/2 inch socket for ER collet chuck 40	309700 40