



## Base body MT shank, with through-coolant, 3×D, Type: 12



### Order data

Order number	232272 12
GTIN	4062406105860
Item class	22G

### Description

#### Version:

With internal cooling.

#### Straight fluted.

#### Note:

For suitable reducing adapters for tools with MT shanks see **No. 343000-343530**.

Further sizes available on request.

Through-coolant: yes

Number of cutting edges Z: 2

Dia. range  $D_c$ : 12 - 12.5 mm

Reach  $L_1$ : 31.8 mm

Morse taper MT size: 2

Clamping screws: 232990 TX7

### Technical description

Clamping screws	232990 TX7
Dia. range $D_c$	12 - 12.5 mm
Morse taper MT size	2
Reach $L_1$	31.8 mm
Number of cutting edges Z	2
Version	3×D
Shank	Morse taper
Through-coolant	yes

Type of product

Indexable drill