



## Base body MT shank, with through-coolant, 12×D, Type: 13



### Order data

Order number	232275 13
GTIN	4062406106058
Item class	22G

### Description

#### Version:

With internal cooling.

#### Note:

For suitable reducing adapters for tools with MT shanks see **No. 343000-343530**.

Further sizes available on request.

Reduce feed rates  $f$  by 10% and  $v_c$  values by 30%.

Through-coolant: yes

Number of cutting edges  $Z$ : 2

Dia. range  $D_c$ : 13 - 17.5 mm

Reach  $L_1$ : 156 mm

Morse taper MT size: 2

Clamping screws: 232990 TX8

### Technical description

Clamping screws	232990 TX8
Dia. range $D_c$	13 - 17.5 mm
Reach $L_1$	156 mm
Morse taper MT size	2
Number of cutting edges $Z$	2
Version	12×D
Shank	Morse taper
Through-coolant	yes
Type of product	Indexable drill

