



## Base body MT shank, with through-coolant, 8xD, Type: 48



### Order data

|              |               |
|--------------|---------------|
| Order number | 232274 48     |
| GTIN         | 4062406106034 |
| Item class   | 22G           |

### Description

#### Version:

For holes up to IT10 accuracy.

With internal cooling. **Straight fluted.**

#### Note:

For suitable reducing adapters for tools with MT shanks see **No. 343000-343530**.

Further sizes available on request.

Reduce feed rates  $f$  by 5% and  $v_c$  values by 10%.

### Technical description

|                             |                 |
|-----------------------------|-----------------|
| Dia. range $D_c$            | 48 - 65 mm      |
| Morse taper MT size         | 5               |
| Reach $L_1$                 | 422.3 mm        |
| Clamping screws             | 232990 TX20     |
| Number of cutting edges $Z$ | 2               |
| Version                     | 8xD             |
| Shank                       | Morse taper     |
| Through-coolant             | yes             |
| Type of product             | Indexable drill |

