

**Garant**
**Arbor for screw-in milling cutters with thread tapered form, HSK-A 63, Thread M × Length L1: M16X75**

**Order data**

Order number	307044 M16X75
GTIN	4062406106898
Item class	31A

**Description**
**Version:**

Tapered design.  
With Balluff/RFID chip bore.

**Application:**

To take screw-in milling cutters with thread.

**Optional extras:**

Extensions No. 301358, reducers No. 301359, coolant pipe No. 309880, socket for coolant pipe No. 309890.

**Note:**

Solid carbide arbors and extensions for screw-in milling cutters No. 301374 – 301379 and No. 301361 – 301368.

**Technical description**

L <sub>2</sub>	5 mm
Bore Ø D <sub>1</sub>	17 mm
Thread M	M16×75
Reach L <sub>1</sub>	75 mm
Ø D <sub>2</sub>	29 mm
External Ø D	34 mm

Overhang dimension A	101 mm
Adapter	HSK-A 63
Arbor standard	DIN 69893
Arbor standard	ISO 12164-1
Shape	A
Balance quality G at rotational speed	G 2.5 at 25,000 rpm
Concentricity	$\leq 3 \mu\text{m}$
Machining strategy	HSC
Type of product	Threaded copy mill arbor