

**Garant**
**Arbor for screw-in milling cutters with thread tapered form, HSK-A 100,  
Thread M × Length L1: M10X150**

**Order data**

Order number	307046 M10X150
GTIN	4062406106959
Item class	31A

**Description**
**Version:**

Tapered design.

With Balluff/RFID chip bore.

**Application:**

To take screw-in milling cutters with thread.

**Optional extras:**

Extensions No. 301358, reducers No. 301359, coolant pipe No. 309880, socket for coolant pipe No. 309890.

**Note:**

Solid carbide arbors and extensions for screw-in milling cutters No. 301374 – 301379 and No. 301361 – 301368.

**Technical description**

Bore $\varnothing D_1$	10.5 mm
Overhang dimension A	179 mm
$\varnothing D_2$	18 mm
Reach $L_1$	150 mm
Thread M	M10×150
$L_2$	10 mm

External Ø D	36.5 mm
Adapter	HSK-A 100
Arbor standard	ISO 12164-1
Arbor standard	DIN 69893
Shape	A
Balance quality G at rotational speed	G 2.5 at 25,000 rpm
Concentricity	≤ 3 µm
Machining strategy	HSC
Type of product	Threaded copy mill arbor