



2-component adhesive, Manufacturer ID: DP8405



Order data

Order number	083374 DP8405
GTIN	051115689635
Item class	08M

Description

Version:

Tough resilient 2-component adhesive for quick and easy jointing, makes a permanent joint. Cures at room temperature. Tough high-impact acrylate adhesive for high-strength bonding of plastics such as ABS, PC, PMMA, and PVC, etc., and metals.

Application:

Use manual application gun No. 083373 size PISTOLE together with delivery piston No. 083375 size KOLBEN10 and mixing tubes No. 083375 size MIXER.

Technical description

Labelling of hazardous substances	GHS02: Flame
Labelling of hazardous substances	GHS07 caution
Labelling of hazardous substances	GHS09 harmful to the environment
Tensile shear strength	17 N/mm ²
Manufacturer's designation	DP8405
Dynamic viscosity	50000 mPas

Colour	green
Working life after date of manufacture	24 mo
Tensile strength	30 N/mm ²
Characteristics	neutral smell
Characteristics	tough and resilient
Processing temperature	20 °C
UN number	UN1133
Chemical basis	Acrylate
hazardous goods class	3
Operating temperature range	-40 °C
Storage temperature	15 °C
Capacity	45 g
Suitable for application area	powder-coated surfaces
Shape	liquid
Suitable for material	Plastic
Suitable for material	Metal
Density	1.07 g/cm ³
Functional strength to	15 min
Touch dry after	14 - 16 min
Maximum gap size	0.3 mm
Resistant to impacts and vibrations	yes
Lap shear strength	30 N/mm ²
Type of product	Two-component adhesive

Accessories

2-component adhesive accessories Version MIXER	083375 MIXER
2-component adhesive accessories Version KOLBEN10	083375 KOLBEN10
Manual dispensing gun Version PISTOLE	083373 PISTOLE

