

Garant
Arbor for screw-in milling cutters with thread tapered form, HSK-A 63, Thread M × Length L1: M10X75

Order data

Order number	307044 M10X75
GTIN	4062406106799
Item class	31A

Description
Version:

Tapered design.
With Balluff/RFID chip bore.

Application:

To take screw-in milling cutters with thread.

Optional extras:

Extensions No. 301358, reducers No. 301359, coolant pipe No. 309880, socket for coolant pipe No. 309890.

Note:

Densimet arbors and solid carbide extensions for screw-in milling cutters No. 301374 – 301379 and No. 301361 – 301386.

Machining strategy: HSC

Overhang dimension A: 101 mm

Bore $\varnothing D_1$: 10.5 mm

$\varnothing D_2$: 18 mm

External $\varnothing D$: 23 mm

Reach L_1 : 75 mm

L_2 : 5 mm

Technical description

Overhang dimension A	101 mm
----------------------	--------

Bore $\varnothing D_1$	10.5 mm
$\varnothing D_2$	18 mm
L_2	5 mm
Thread M	M10×75
External $\varnothing D$	23 mm
Reach L_1	75 mm
Adapter	HSK-A 63
Arbor standard	DIN 69893
Arbor standard	ISO 12164-1
Shape	A
Balance quality G at rotational speed	G 2.5 at 25,000 rpm
Concentricity	$\leq 3 \mu\text{m}$
Machining strategy	HSC
Type of product	Threaded copy mill arbor