

Garant**Arbor for screw-in milling cutters with thread tapered form, HSK-A 100,
Thread M × Length L1: M16X50****Order data**

Order number	307046 M16X50
GTIN	4062406106997
Item class	31A

Description**Version:**

Tapered design.

With Balluff/RFID chip bore.

Application:

To take screw-in milling cutters with thread.

Optional extras:

Extensions No. 301358, reducers No. 301359, coolant pipe No. 309880, socket for coolant pipe No. 309890.

Note:

Solid carbide arbors and extensions for screw-in milling cutters No. 301374 – 301379 and No. 301361 – 301368.

Technical description

Overhang dimension A	79 mm
Thread M	M16×50
Ø D ₂	29 mm
External Ø D	34 mm
Reach L ₁	50 mm
Bore Ø D ₁	17 mm

L ₂	5 mm
Adapter	HSK-A 100
Arbor standard	ISO 12164-1
Arbor standard	DIN 69893
Shape	A
Balance quality G at rotational speed	G 2.5 at 25,000 rpm
Concentricity	≤ 3 μm
Machining strategy	HSC
Type of product	Threaded copy mill arbor