



## FlyMarker® mini 120/45 needle marker Cordless, Battery capacity: 2X8A-h



### Order data

Order number	085761 2X8
GTIN	
Item class	04F

### Description

#### Version:

For permanent identification / marking / lettering of batch and series production parts of different materials (steel, stainless steel, aluminium, copper, brass, plastics, tool steel, hardened steels up to 62 HRC, etc.).

- **Powerful electro-magnetic marking needle drive.**
- **Simple intuitive software with password protection.**
- **Interfaces: USB-A, USB-B and Ethernet.**
- **Font: Dot matrix in a 5×7 or 9×13 grid, font height 1.0 – 10.0 mm and larger.**
- **Fonts for character heights greater than 10.0 mm on request.**
- **High-quality double linear guides for precise marking results.**
- **Round parts can be marked radially and axially, and also in an arc of a circle.**
- **Supplied with an HPGL package (for marking individual logos and inspection symbols, CE marks etc.)**
- **Supplied with a convenience package (e.g. for shift identification, pre-positioning, multiple marking, etc.)**
- **Internal memory for several hundred marking files, fonts and logos.**
- **Available in 15 languages.**
- **High-resolution colour display.**
- **Marking preview for reliable marking.**
- **Unbreakable housing.**

**FlyMarker® mini 120/45 18 V.** Extremely handy, 100% mobile **cordless manual marking system** with integral keyboard and high-resolution LC colour display. Marking field: 120 × 45 mm.

- **More stable guidance system.**
- **Extra strong attachment magnet (optional).**

**Supplied with:**

Including tool kit, solid carbide marking needle 90° adjustment bracket with non-slip coating, setting gauge, and carrying case. **2×18 V Li-ion rechargeable batteries**, charger.

maximum marker field height: 45 mm

Battery capacity: 8 A·h

Nominal voltage: 18 V

Weight including rechargeable battery: 3.7 kg

### Technical description

Battery capacity	8 A·h
Manufacturer's designation	FlyMarker® mini 120/45
Number of rechargeable batteries contained	2
Power supply	Rechargeable battery-powered
Type of rechargeable battery	Lithium-ion
Weight including rechargeable battery	3.7 kg
Nominal voltage	18 V
maximum marker field width	120 mm
maximum marker field height	45 mm
Type of product	Needle marker

### Accessories

Interchangeable battery Type 8AH	085765 8AH
----------------------------------	------------