

Garant**Support frame, for insert size length×width: 1000X630mm****Order data**

Order number	431000 1000X630
GTIN	
Item class	41C

Description**Version:**

Sturdy welded construction including levelling fittings. Uneven floors can be compensated using height compensation screws..

Support frame, steel sections, paint finish RAL 9006 white aluminium. Beech ply storage shelf.

Application:

The natural granite tables No. 430190 - 430500 are mounted on pre-determined points (steel ball inserts).

- **For plates up to 630×630 mm. For setting up on workbenches and the like, adjustable screw jacks No. 373500 are most suitable.**
- **The support jacks are adjustable for height and allows the table to be levelled (3-point contact and 2 support screws as protection against tipping)**

Note:

For vibration-absorbing machine mounts, please order 4× No. 086002 size 850.

Technical description

Support cabinet width	750 mm
suitable for worktop size length×width	1,000×630 mm
Support cabinet depth	560 mm

Weight	31 kg
Support cabinet height	720 mm
Load capacity, distributed	1000 kg
Material of storage shelf	Beech ply
maximum working height (top face of the granite table)	900 mm
Height of support cabinet incl. bearing sets	780 mm
Height adjustment	25 mm
Type of product	Sub-frame