

**PLANOLITH**
**Granite plate Accuracy class 1, Length×Width: 1000X630mm**

**Order data**

Order number	430200 1000X630
GTIN	2050001949721
Item class	46H

**Description**
**Version:**

Specially selected natural granite.

- **Free from defects, homogeneous structure.**
- **Resistant to deflection and to warping.**
- **Absolutely rust-proof and acid resistant, low thermal conductivity.**
- **Micro-fine machine surface (diamond lapped). Within all the permissible tolerances.**
- **Ground outside edges, visually true.**
- **For mounting as determined statically, contact points (steel ball inserts) are fitted to the underside.**
- **Harder than hardened steel (Mohs hardness scale 6 – 7), non-magnetic and electrically non-conductive.**

**Accuracy:**

Final manufacturing and inspection take place in computer-controlled climatic rooms. The used measuring equipment guarantees the exact connection to national and international calibration laboratories.

**DIN 876/1 – diamond lapped** for workshop and production.

**Supplied with:**

**Supplied with test certificate, transport packing.** Including steel ball inserts.

**Note:**

**On request:** Stainless steel screw inserts, steel T-slot rails (steel T-slot rails not available for No. 430190), accuracy 000, other sizes, intermediate sizes. Delivery excluded.

**Technical description**

Weight	189 kg
Thickness	100 mm

Flatness	0.02 mm
Number of steel ball inserts	3
Standard	DIN 876
Accuracy	1 mm
Test certificate	Manufacturer's test certificate
Type of product	Graduated plate

---

## Accessories

Support cabinet for insert size length×width 1000X630 mm	431050 1000X630
--	-----------------