



Weldon arbor for screw-in milling cutters with internal coolant supply, $\varnothing d = 20$ mm, Thread M \times Length L1: M10X97



Order data

| | |
|--------------|---------------|
| Order number | 301347 M10X97 |
| GTIN | 4062406107352 |
| Item class | 32A |

Description

Version:**Shank tolerance h6.****Application:**

For mounting in side lock arbors (Weldon).

Technical description

| | |
|------------------------|--------------------------|
| Bore $\varnothing D_1$ | 10.5 mm |
| L_2 | 81.4 mm |
| $\varnothing D_2$ | 18 mm |
| Reach L_1 | 97 mm |
| Overall length L | 152 mm |
| Adapter | $\varnothing d = 20$ mm |
| Through-coolant | yes |
| Type of product | Threaded copy mill arbor |