



## Solid carbide high performance drill Whistle-Notch shank DIN 6535 HE, TiN, Ø DC h7: 10,2mm



### Order data

Order number	122640 10,2
GTIN	4045197395986
Item class	12E

### Description

#### Version:

Cutting chisel edge with **high centring accuracy** due to **strong core and special point geometry**.

**Straight major cutting edges** with slightly honed edges and special flute profile produce **short chips**.

#### Note:

Flute length  $L_c = L_2 + 1.5 \times D_c$ .

**NEW GENERATION AVAILABLE!**

**Recommended successor product is No. 122778.**

### Technical description

Number of cutting edges Z	2
Feed f in steel < 900 N/mm <sup>2</sup>	0.22 mm/rev.
Flute length $L_c$	71 mm
Shank tolerance	h6
Nominal Ø $D_c$	10.2 mm
Tolerance nominal Ø	h7
Shank Ø $D_s$	12 mm
Overall length L	118 mm
Standard	DIN 6537

recommended maximum drilling depth $L_2$	55.7 mm
Coating	TiN
Tool material	Solid carbide
Version	6×D
Point angle	140 degrees
Shank	DIN 6535 HE to h6
Through-coolant	yes, with 25 bar
Colour ring	green
Type of product	Jobber drill

### User data

	Suitability	$V_c$	ISO code
Aluminium (short chipping)	suitable only under restricted conditions	240 m/min	N
Steel < 500 N/mm <sup>2</sup>	suitable	110 m/min	P
Steel < 750 N/mm <sup>2</sup>	suitable	90 m/min	P
Steel < 900 N/mm <sup>2</sup>	suitable	80 m/min	P
Steel < 1100 N/mm <sup>2</sup>	suitable only under restricted conditions	65 m/min	P
Steel < 1400 N/mm <sup>2</sup>	suitable only under restricted conditions	30 m/min	P
INOX < 900 N/mm <sup>2</sup>	suitable	35 m/min	M
INOX > 900 N/mm <sup>2</sup>	suitable	30 m/min	M
Ti > 850 N/mm <sup>2</sup>	suitable	30 m/min	S
Uni	suitable		
wet maximum	suitable		
wet minimum	suitable		
Air	suitable only under restricted conditions		

