



## Weldon arbor for screw-in milling cutters with internal coolant supply, $\varnothing d = 20$ mm, Thread M $\times$ Length L1: M6X25



### Order data

Order number	301347 M6X25
GTIN	4062406107338
Item class	32A

### Description

#### Version:

Shank tolerance h6.

#### Application:

For mounting in side lock arbors (Weldon).

### Technical description

Bore $\varnothing D_1$	6.5 mm
$\varnothing D_2$	10 mm
Reach $L_1$	25 mm
$L_2$	5 mm
Overall length L	75 mm
Adapter	$\varnothing d = 20$ mm
Through-coolant	yes
Type of product	Threaded copy mill arbor