

**Garant****Support frame, for insert size length×width: 2000X1000mm****Order data**

Order number	431000 2000X1000
GTIN	4045197720665
Item class	41C

**Description****Version:**

Sturdy welded construction including levelling fittings. Uneven floors can be compensated using height compensation screws..

**Support frame**, steel sections, paint finish RAL 9006 white aluminium. Beech ply storage shelf.

**Application:**

The natural granite tables No. 430190 - 430500 are mounted on pre-determined points (steel ball inserts).

- **For plates up to 630×630 mm. For setting up on workbenches and the like, adjustable screw jacks No. 373500 are most suitable.**
- **The support jacks are adjustable for height and allows the table to be levelled (3-point contact and 2 support screws as protection against tipping)**

**Note:**

For vibration-absorbing machine mounts, please order 4× No. 086002 size 850.

Height adjustment: 25 mm

Support cabinet height: 720 mm

Support cabinet width: 1460 mm

Support cabinet depth: 830 mm

Height of support cabinet incl. bearing sets: 780 mm

Load capacity, distributed: 2000 kg

Weight: 66 kg

## Technical description

Weight	66 kg
Load capacity, distributed	2000 kg
Support cabinet height	720 mm
suitable for worktop size length×width	2000×1000 mm
Support cabinet width	1460 mm
Support cabinet depth	830 mm
Material of storage shelf	Beech ply
maximum working height (top face of the granite table)	900 mm
Height of support cabinet incl. bearing sets	780 mm
Height adjustment	25 mm
Type of product	Sub-frame