



Claw jaws set, 3 pieces, for chucks, Ø 200 mm, Type: 1



Order data

Order number	313231 1
GTIN	2050001929273
Item class	33T

Description

Application:

As the jaws can be changed or adjusted to the required diameter **in just a few seconds**, it is useful to have several jaw sets on hand ready for use at the machine. **This minimises set-up times.** The jaw units consist for example of several sets of base jaws with soft top jaws, which can be machined out to the required diameters. This rationalisation method is not only necessary for NC machines but also important for every lathe type.

For external clamping, ideally suited to clamping blanks.

Material:

Quality product made of 16MnCr5, hardened.

Suitable for:

Schunk self-centring chucks No. 313115; 313117; 313135; 313137, Röhms self-centring chucks Duro No. 313120; 313140 and other self-centring chuck systems.

Note:

Example of clamping range of No. 313115 - 313137. Depth of the clamping step 25 mm.

Technical description

Clamping range	34 - 99 mm
for chuck type Ø	200 mm
Product name attribute	Ø 200 mm
Slot width D	10 mm
Bore spacing b	40 mm

Tenon length A	20 mm
suitable for colour code	Schunk self-centring chucks and jaws
suitable for colour code	Röhm self-centring chucks and jaws
Type of product	Self-centring chuck jaws