## Garant

## Support cabinet, for insert size length×width: 1500X1000 mm



## Order data

Order number	431050 1500X1000
GTIN	4045197720696
Item class	41C

### Description

#### Version:

Sturdy welded construction including levelling fittings. Uneven floors can be compensated using height compensation screws.

**Support cabinet,** casing made from sheet steel, with swing-door (including storage shelf) and/ or drawers depending on size, including GARANT locking system. Paint finish of the shell RAL 9006 aluminium white, front faces RAL 5011 steel blue.

#### **Application:**

The natural granite tables No. 430190 - 430500 are mounted on pre-determined points (steel ball inserts).

- For plates up to 630×630 mm. For setting up on workbenches and the like, adjustable screw jacks No. 373500 are most suitable.
- The support jacks are adjustable for height and allows the table to be levelled (3-point contact and 2 support screws as protection against tipping)

#### Fitted with:

Drawer front height (right): 60; 100; 120; 200 mm

Door height (left): 480 mm

#### Note:

For vibration-absorbing machine mounts, please order 4× No. 086002 size 850.

Cylinder lock: modular barrel

Support cabinet height: 720 mm

Support cabinet width: 1304 mm

Support cabinet depth: 780 mm

Height of support cabinet incl. bearing sets: 780 mm Drawer usable width: 490 mm Drawer usable depth: 520 mm

# **Technical description**

Support cabinet depth	780 mm
Number of drawers	4
Drawer usable depth	520 mm
suitable for worktop size length×width	1500×1000 mm
Weight	137 kg
Drawer usable width	490 mm
Support cabinet height	720 mm
Support cabinet width	1304 mm
Load capacity, distributed	2000 kg
Number of doors	1
Electronic locking system can be retrofitted	yes
maximum working height (top face of the granite table)	900 mm
Height of support cabinet incl. bearing sets	780 mm
Drawer/pull-out shelf load capacity	100 kg
Drawer runner extension (partial/full extension)	90 %
Height adjustment	25 mm
Hoffmann perforated panel grid interval	9×9
Cylinder lock	modular barrel
Type of product	Base cabinet for measurement technology