



Torque screwdriver TorqueVario®, maximum torque: 1400cNm



Order data

Order number	659930 1400
GTIN	4010995396909
Item class	63K

Description

Version:

Numerical display of the torque value via scale in the window (40 – 50 individual values, depending on the torque range). Torque continuously adjustable using Torque-Setter (included). On reaching the set torque value, the screwdriver can be felt and heard to trigger and is then immediately ready for use again. Accuracy class $\pm 6\%$.

Application:

With T-handle and bit holder for 1/4 inch bits.

Standard:

Geprüft nach DIN EN ISO 6789.

Note:

The guaranteed measuring accuracy of the torque is achieved only once the torque range has been calibrated to DIN EN ISO 6789.

Setting standard for size 60-700: No. 659931 size1 and for size 1400: No. 659931 size 2.

Technical description

Display	analogue
maximum torque	1400 cNm
Torque measuring accuracy	$\pm 6\%$
Bit socket	D 6,3

Bit socket	F 6.3
Torque range	500 - 1400 cNm
Torque range	5 - 14 Nm
Adjustable trigger value	preset
Measurement process	Torque
Weight	560 g
Connection format	Bit holder 1/4 inch
Setting the trigger value	with adjustment scale
Reversible reading	Nm
Feedback	triggering
Standard	DIN EN ISO 6789
Trigger principle	mechanical short-travel release
Overall length L	120 mm
Series	TorqueVario®
Calibration	O1
Direction of tightening	Right-hand tightening
Test certificate	Manufacturer's test certificate
Data can be recorded	no
Release signalling	akustisk
Release signalling	haptisk
Measurement technology	mechanical
Manufacturer's designation	TorqueVario®-S T
Torque fixed setting	no
Type of product	Torque screwdriver

Services

Calibration Torque screwdriver maximum torque 0,04-20 N·m

020200 0,04-20

Accessories

Adjustment tool Torque Setter Type 2

659931 2