


Combidisc® CONTOUR grinding disc, 60 mm Ø, Grit: 120

Order data

Order number	554034 120
GTIN	4007220898864
Item class	55G

Description
Version:

The Roloc™, Combidisc® CDR **quick-change system** with a plastic external thread permits safe abrasive tool changing "with a single twist of the wrist" in a very short time.

Disc with protruding waved edges **for fine grinding of contours and concave surfaces.**

Application:

For efficient abrasion of small areas, even with changing contours. Reduced tool changing times save costs on multi-stage operations.

Use in conjunction with soft support pad No. 554091 50.

Note:

Roloc™ bristle discs can be found from No. 573510 onwards.

Technical description

Grit	120
Disc Ø	60 mm
Grinding media	Aluminium Oxide (A)
Grinding medium code	A
Product name attribute	60 mm Ø

maximum speed	20000 min ⁻¹
Type of product	Grinding wheel

User data

	Suitability	V _c	ISO code
Alu Mg	suitable only under restricted conditions		
Steel < 900 N/mm ²	suitable		
Steel < 1400 N/mm ²	suitable		
Steel < 55 HRC	suitable		
Steel < 60 HRC	suitable only under restricted conditions		
INOX	suitable only under restricted conditions		
Ti	suitable only under restricted conditions		
GG(G)	suitable		
CuZn	suitable only under restricted conditions		
dry	suitable		

Accessories

Rubber backing pad shank Ø 6 mmsoft External Ø 50 mm	554091 50
--	-----------