



Pneumatic angle grinder, Type: 3650-120

Order data

Order number	079315 3650-120
GTIN	15451701253
Item class	03R

Description

Version:

- **1.5 HP motor with 1100 W power.**
- **Protective hood adjustable without using tools.**
- **125 mm disc capacity.**
- **Aesthetic streamlined safety handle.**

Compact and **powerful** angle grinder for very long service life on heavy-duty applications, up to 1000 hours maintenance intervals. Ergonomic and vibration-damped handle. Protective hood adjustable without using tools. **M14 spindle thread.**

Output power: 1700 W

maximum speed: 12000 rpm

maximum air consumption: 1920 l/min

Thread of the compressed air connection port: 3/8" NPT inch

recommended hose size (internal Ø): 13 mm

Minimum disc Ø: 125 mm

Technical description

Warranty period for the machine	a
Type of product	