



Burr Tooth profile STEEL – coarse, Carbide, Type: C1625



Order data

Order number	547100 C1625
GTIN	4007220003022
Item class	55F

Description

Version:

The innovative tooth geometry permits **very high metal removal rates** combined with **smooth cutting and good guidance accuracy**. The optimised chip formation (no pointed chips) ensures good surface quality. Shank Ø 6 mm.

Application:

Optimised for **use on steel and steel castings**.

Shank Ø: 6 mm

Shape description: ball nose

Head Ø: 16 mm

Head length L_1 : 25 mm

Overall length: 70 mm

Shank Ø: 6 mm

Technical description

Shape description	ball nose
Head Ø	16 mm
Shape	C1625
Overall length	70 mm
Head length L_1	25 mm
Toothing grit designation	coarse
Tooth type abbreviation	STEEL
Shank Ø	6 mm

Tool material	Carbide
Type of product	Burr